



With your health in mind

Munters media are GREENGUARD GOLD Certified




Indoor air quality concerns us all

Did you know that we spend more than 90% of our time indoors?

This means we receive the majority of our environmental exposure to chemicals indoors. The largest source of indoor air pollution is chemical emissions from building materials and furnishings.

It's hard to control the outdoor pollution we encounter, but we certainly can do something about our indoor air.

Choosing certified media and rotors from Munters is an easy action to take towards creating your own perfect climate.




At home



A healthy indoor air prevents

- Asthma and allergies
- Headaches
- Respiratory disease
- Eye, nose & throat irritation
- Reproductive/developmental defects
- Neurological disease
- Some forms of cancer


In the office



At school



In the industry



At the supermarket



Make it safer to breathe

Munters CELdek® and GLASdek®


To ensure the air passing through our media and rotors is safe to breath, Munters media and rotor material are GREENGUARD GOLD Certified


What is GREENGUARD?

Products are tested by the independent company, UL, for emissions of volatile organic compounds (VOCs). UL's goal is to improve public health and quality of life through programs that reduce chemical exposure and improve indoor air. This is the most stringent product emissions standards in the world.

Munters media and rotor material have been tested for 364 chemicals of concern and certified for being free from harmful substances.

You can read more about GREENGUARD and UL on www.ul.com





An international name, where the customer comes first.

Munters, listed on Nasdaq Stockholm, has offices in 30 countries and around 3,500 employees in many branches around the world. We are global leaders in energy efficient air treatment for comfort, process and environmental protection. Munters shares ideas within its international network, giving the Group an outstanding reputation as a reliable, fast-acting and customer-orientated expert in air conditioning. Munters philosophy of customer satisfaction is central to our decision-making. When developing and manufacturing our systems, we see happy customers as our number one target. And this is what our employees strive to ensure every day.

For more information on Munters, please visit www.munters.com

Australia Phone +61 2 8843 1588, dh.info@munters.com.au **Austria** Phone +43 1 6164298-0, luftentfeuchtung@munters.at **Belgium** Phone +32 1528 5611, info@muntersbelgium.be **Brazil** Phone +55 41 3317 5050, munters@com.br **Canada** Phone +1 905 858 5894, dhinfo@munters.com **China** Phone +86 10 8041 8000, info@munters.com.cn **Czech Republic** Phone +420 544 211 434, info@munters-odvlhcovani.cz **Denmark** Phone +45 4495 3355, info@munters.dk **Finland** Phone +358 20 776 8230, laitemyynti@munters.fi **France** Phone +33 1 3411 5757, dh@munters.fr **Germany** Phone +49 4087 96900, mgd@munters.de **India** Phone +91 20 668 18 900, info@munters.in **Italy** Phone +39 0183 52 11, marketing@munters.it **Japan** Phone +81 3 5970 0021, mkk@munters.co.jp **Korea** Phone +82 2761 8701, munters@munters.co.kr **Mexico** Phone +52 722 270 40 49, munters@munters.com.mx **Netherlands** Phone +31 172 433231, vochtbeheersing@munters.nl **Poland** Phone +48 58305 3517, dh@munters.pl **Singapore** Phone +65 6744 6828, info@munters.com.sg **South Africa** Phone +27 11 997 2000, info@munters.co.za **Spain** Phone +34 91 640 09 02, marketing@munters.es **Sweden** Phone +46 8 626 63 00, avfuktning@munters.se **Switzerland** Phone +41 52 343 8886, info.dh@munters.ch **Thailand** Phone +66 2642 2670, info@munters.co.th **Turkey** Phone +90 216 548 1444, info@muntersform.com **UAE** +971 4887 6462, middle.east@munters.com **United Kingdom** Phone +44 1480 432243, info@munters.co.uk **USA** Phone +1 978 241 1100, dhinfo@munters.com **Vietnam** Phone +84 8 8256 838, vietnam@muntersasia.com

Your closest distributor

www.munters.com/greenguard

