

Product guide
DryCool™ DuraCase

- Rugged shipping container
- Cool, dry supply air
- High COP
- Easy to move and install
- Low maintenance




DryCool™ DuraCase

Munters DryCool™ DuraCase provides operators the ability to control temperature and humidity independently from a fully transportable container. The durable shipping container serves as the housing for the efficient DryCool™ system.

The DryCool™ system combines the benefits of desiccant dehumidifiers with the cooling of DX air conditioners to treat make up air. Designed to cost-effectively treat 100% makeup air, the system controls humidity on an as-needed basis.



DryCool™ DuraCase Illustration




The DryCool™ DuraCase operates cost-efficiently because all of the energy required for the operation of its desiccant dehumidifier is recycled from cooling components. DuraCase lowers energy costs as the Coefficient of Performance (COP) is higher than a typical air conditioning system.

DuraCase is designed for transport with all replaceable components accessible through hinged doors and built in supply air duct ports for quick installation of flexible duct work. This rugged unit can easily be relocated without the concern of it becoming damaged.

These units are packaged to include a direct expansion cooling coil, a desiccant wheel, integrated condensing package, supply fan, reactivation fan and condensing fans.

DryCool™ DuraCase Unit Airflow

	A	B	C	D	E	F
DB °F	93	59	75	77	92	123
WB °F	84	59	60	61	84	90
gr/lb	163.8	74.2	54.6	54.6	193.8	163.8



Australia Munters Pty Limited, Phone +61 2 6025 6422, Fax +61 2 6025 8266, Austria via sales organization in Germany, Brazil Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, Fax +55 41 3317 5070, Canada Munters Canada Inc., Phone +1 416 271 9657, China Munters Air Treatment Equipment (Beijing) Co., Ltd., Phone +86 10 80 481 121, Fax +86 10 80 483 493, Denmark via sales organization in Sweden, Finland Munters Oy, Phone +358 9 83 86 030, Fax +358 9 83 86 0336, France Munters France S.A., Phone +33 1 34 11 57 50, Fax +33 1 34 11 57 51, Germany Munters Euroform GmbH, Phone +49 241 89 00 0, Fax +49 241 89 00 5199, Indonesia Munters, Phone +62 21 9105446-7, Fax +62 21 5310509, Italy Munters Italy S.p.A., Phone +39 0183-52 11, Fax +39 0183-521 333, Japan Munters K.K., Phone +81 3 5970 0021, Fax +81 3 5970 3197, Kingdom of Saudi Arabia and Middle East Hawa Munters, c/o Hawa United Cooling Syst. Co. Ltd., Phone +966 1 477 15 14, Fax +966 1 476 09 36, Korea Munters Korea Co., Ltd, Phone +82 2 761 8701, Fax +82 2 761 8777, Mexico Munters Mexico Phone +52 722 270 40 30, Fax +52 722 270 41 95, Norway via sales organization in Sweden, South Africa and Sub-Sahara Countries Munters (Pty) Ltd, Phone +27 11 997 2000, Fax +27 11 608 3501, Spain Munters Spain S.A., Phone +34 91-640 09 02, Fax +34 91-640 11 32, Sweden Munters Europe AB, Phone +46 8 626 63 00, Fax +46 8 754 56 66, Switzerland via sales organization in Germany, Thailand Munters (Thailand) Co. Ltd., Phone +66 2 645 2708-12, Fax +66 2 645 2710, United Kingdom Munters Ltd, Phone +44 845 644 3980, Fax +44 845 644 3981, United States Munters Corporation, Phone +1 800 843 5360, Export & other countries Munters, Phone +46 8 626 63 00, Fax +46 8 754 56 66.



Your closest distributor
Munters Corporation
 Tel: (800) 843-5360 E-mail: dhinfo@munters.com www.munters.us