



Product guide
R-Series | 5,000, 10,000 & 15,000 SCFM

- Rugged and longer lasting construction compared to foam panel systems
- Durable construction designed to withstand frequent movement and transportation
- 15–30% less energy consumption compared to other suppliers
- Lower dew points are achieved through Munters' 400 mm rotor
- Dual reactivation provides utility source flexibility at customer site


R-Series Rental Dehumidifiers

Munters R-Series dehumidifiers provide the rental industry with a line of reliable and durable dehumidification systems built for ease of mobility and flexibility to meet a wide variety of customer requirements and applications.

Each system contains Munters' patented Honeycombe® desiccant rotor technology and is available in sizes of 5,000 SCFM, 10,000 SCFM or 15,000 SCFM.



R-Series Configuration



Drawing above represents R-5000 model. Configuration and design is similar for other models within this product series.

Features

- Minimum 1/8" aluminum all-welded construction
- Cage is designed to bolt directly to skid with top-of-cage certified lifting lugs
- Integral forklift pockets and lifting points
- R-5,000 and R-10,000 designed to be stackable
- 400mm deep Silica Gel rotor
- Gas and electric dual reactivation
- Natural gas and propane single gas train selector switch
- Cam lock power connections
- Chain wheel drive
- Dry air fans provide 5" W.C. external static pressure at maximum volumes and higher at lower volumes
- 18"/20" round connection with tethered plastic inlet/outlet covers work as lay-flat duct holders when ducting is required
- User instructions and unit flow diagram (with red and green status lights for reactivation temp, wheel drive, process fan, etc.) located directly on units
- ETL/UL approved

Rental Units Performance Table

Unit	Air Flow, Nominal CFM	Moisture Removal 80 °F, 60% RH (lb/hr)	Efficiency (BTUH per lb of H ₂ O removed)	Dry Air External Static Pressure	Dimensions LxWxH (in.)	Weight (lb)	Power	Power Required, Full Load Amps	Dry Air Duct Connections	Recommended Generator Size, kW (kVA)	Gas Reactivation Available
R-5,000	5,000	157	1826	5.0" ESP	99 x 52 x 100	3,600	460v/3/60	125	18" or 20"	100 kW (125)	Electric and Gas
R-10,000	10,000	330	1861	5.0" ESP	180 x 90 x 100	7,500	460v/3/60	282	(2) 18"/20" Returns, (2) 18"/20" Supply	225 kW (250)	Electric and Gas
R-15,000	15,000	405	1955	5.0" ESP	211 x 88 x 104	11,200	460v/3/60	380	(3) 18"/20" Returns, (3) 18"/20" Supply	303 kW (320)	Electric and Gas

Options for Munters R- (Rental) Products:

Round Inlet & Outlet Duct Connections: 18" or 20"

Cage: Yes or No

Power: 480v/3/60 and 575/3/60 (for Canada)

React: Optional Gas Only. Optional Electric Only.

Skid & Cage Finish: Painted Steel or Hot Dipped

Galvanized

Unit Color: Gray is standard. Custom colors available.

Munters invented the desiccant rotor technology and provides its rental equipment customers with over 60 years of application, selection and energy optimization expertise and support.

Australia Munters Pty Limited, Phone +61 2 6025 6422, Fax +61 2 6025 8266, Austria via sales organization in Germany, Brazil Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, Fax +55 41 3317 5070, Canada Munters Canada Inc., Phone +1 416 271 9657, China Munters Air Treatment Equipment (Beijing) Co., Ltd., Phone +86 10 80 481 121, Fax +86 10 80 483 493, Denmark via sales organization in Sweden, Finland Munters Oy, Phone +358 9 83 86 030, Fax +358 9 83 86 0336, France Munters France S.A., Phone +33 1 34 11 57 50, Fax +33 1 34 11 57 51, Germany Munters Euroform GmbH, Phone +49 241 89 00 0, Fax +49 241 89 00 5199, Indonesia Munters, Phone +62 21 9105446-7, Fax +62 21 5310509, Italy Munters Italy S.p.A., Phone +39 0183-52 11, Fax +39 0183-521 333, Japan Munters K.K., Phone +81 3 5970 0021, Fax +81 3 5970 3197, Kingdom of Saudi Arabia and Middle East Hawa Munters, c/o Hawa United Cooling Syst. Co. Ltd., Phone +966 1 477 15 14, Fax +966 1 476 09 36, Korea Munters Korea Co., Ltd, Phone +82 2 761 8701, Fax +82 2 761 8777, Mexico Munters Mexico Phone +52 722 270 40 30, Fax +52 722 270 41 95, Norway via sales organization in Sweden, South Africa and Sub-Sahara Countries Munters (Pty) Ltd, Phone +27 11 997 2000, Fax +27 11 608 3501, Spain Munters Spain S.A., Phone +34 91-640 09 02, Fax +34 91-640 11 32, Sweden Munters Europe AB, Phone +46 8 626 63 00, Fax +46 8 754 56 66, Switzerland via sales organization in Germany, Thailand Munters (Thailand) Co. Ltd, Phone +66 2 645 2708-12, Fax +66 2 645 2710, United Kingdom Munters Ltd, Phone +44 845 644 3980, Fax +44 845 644 3981, United States Munters Corporation, Phone +1 800 843 5360, Export & other countries Munters, Phone +46 8 626 63 00, Fax +46 8 754 56 66.



Your closest distributor

Munters Corporation

Tel: (800) 843-5360 E-mail: dhinfo@munters.com www.munters.us