



Case study: AIR TREATMENT  
Energy Recovery in the Printing Industry

BENEFITS

- Continuous savings, 365 days/year
- Rapid payback
- Low maintenance
- Increased performance of printing presses
- Eliminates negative pressure problems

## Printing press scores energy savings

A Wisconsin printer using flexographic printing equipment was experiencing air balance problems in the printing plant. Problems included drafts and high energy

bills associated with negative air situations. Rather than simply addressing the air deficit with a traditional gas fired makeup unit, an approach was formulated to


capture much of the energy in the printer exhaust air stream with Munters air-to-air heat exchangers.



## 85 Series Heat Exchanger: Printing Press Heat Recovery

### Energy Source

### Annual Energy Savings/85M06



### The Problem

The printing industry uses diverse technologies to produce a wide variety of printed materials such as magazines and product labels. From lithography and flexography to screen printing, the many different printing processes share some common production and environmental challenges. Among these are the wise use of energy, maintenance of good indoor air quality, and year-round control of temperature and humidity in the facility.

In the Wisconsin plant, the web presses required approximately 23,000 cubic feet per minute (cfm) of air to dry the ink on the printed material. Air from the plant was drawn into the presses, warmed by electric heaters in the presses to about 160°F, and exhausted to the outside. This wasted energy could have easily been captured to help increase production and profits.


### The Solution

Energy recovery technology like air-to-air heat exchangers has been used in the printing industry to improve the overall performance of production by reclaiming otherwise wasted energy.

There were many benefits to using the Munters energy recovery system at the Wisconsin plant. Most importantly, the negative pressure problem in the plant was eliminated. Gas-fired heaters that were needed to maintain temperatures in the plant were shut down, reducing gas consumption and reducing maintenance costs.

A major part of the energy savings stems from the fact that the electric heaters in the press do not have to operate as frequently. On a typical winter day, the heat recovery system raises the 32°F outside air to 98°F and this preconditioned air is supplied directly to the presses. Much of the heating of the outside air had been done with expensive electricity.

Over \$80,000 of annual energy savings make good economic sense. It is also a responsible step to take in terms of environmental benefits and conservation of resources.



Precise humidity control and heat recovery systems for printing plants can help achieve annual energy savings of over \$80,000 per year.

## Other Product Applications in the Printing Industry

Heat recovery ventilation systems (HRVs) have also been used to provide healthy levels of ventilation to improve indoor air quality. In addition, this same heat recovery technology is used in products like the Wringer™ to control humidity in printing plants.


### Indoor Air Quality

Heat recovery ventilators can be used to provide the proper levels of ventilation without paying a large penalty in energy costs. Some units can also help to reduce summer cooling costs. Good indoor air quality is an important component of a healthy, productive work environment.

### Humidity Control

Humidity levels that are too high can create problems with paper stocks and the drying time of inks which can reduce productivity. The Wringer™ uses heat recovery technology to “wring” additional moisture out of the air and reduces the size and operating cost of the dehumidification equipment.

Optional humidification can be added to take care of overly dry winter conditions.



Australia Phone +61 2 8843 1580, serviceair@munters.com.au Austria Phone +43 1 6164298-0, service.dh@munters.at Belgium & Luxembourg Phone +32 2 240 6868, service.dh@muntersnv.be Brazil Phone +55 41 3317 5050, munters@com.br Canada Phone +1 905 858 5894, dhinfo@munters.com China Phone +86 10 8041 8000, serviceair@munters.cn Czech Republic Phone +420 544 211 434, servicecz@munters.de Denmark Phone +45 4495 3355, service.dh@munters.dk Finland Phone +358 40 186 3074, service.dh@munters.fi France Phone +33 1 3411 5757, service.dh@munters.fr Germany Phone +49 40 87 96 90-0, service.dh@munters.de India Phone +91 20 6681 8900, serviceair@munters.in Italy Phone +39 0183 521 377, service.dh@munters.it Japan Phone +91 3 5970 0021, serviceair@munters.jp Korea +82 2 761 8701, serviceair@munters.co.kr Mexico Phone +52 722 270 4029, servicedhm@munters.com Netherlands Phone +31 172 43 32 31, service@munters.nl Poland Phone +48 58 305 35 17, service.dh@munters.pl Singapore Phone +65 6744 6828, serviceair@munters.com.sg South Africa Phone +27 11 971 9700, info@munters.co.za Spain & Portugal Phone +34 91 640 09 02, service.dh@munters.es Sweden & Norway Phone +46 8 626 6300, service.dh@munters.se Switzerland Phone +41 52 3438886, service.dh@munters.ch Thailand Phone +66 2 6422 6703, serviceair@munters.com.sg Turkey Phone +90 216 548 1444, serviceair@munters.com.tr UAE +971 4881 3026, middle.east@munters.com United Kingdom & Ireland Phone +44 1480 432243, service.dh@munters.co.uk USA Phone +1 978 241 1100, dhservice@munters.com Vietnam Phone +84 8 3825 6838, vietnam@muntersasia.com



### Munters Corporation

Tel: (800) 843-5360 E-mail: dhinfo@munters.com  
www.munters.com