

DEW Series Modular Desiccant Dehumidifiers

Benefits


- Weather-tight construction for indoor or outdoor use
- Low profile cassette design
- Quick access for easy maintenance
- Easy duct connections
- Modulating electric, gas or steam reactivation
- Multiple blower orientations
- Optional built-in bypass
- Add-on post/pre-air treatment options

DEW Series Modular Desiccant Dehumidifiers

The Munters DEW series modular dehumidifier provides end users the essential dehumidification function in capacities of 600 to 12,000 scfm. Along with the basic HoneyCombe® rotor-drive-and-seal assembly, DEW offers your choice of process and reactivation fan and either gas, steam or electric reactivation.

Customers can integrate the desiccant dehumidifier into their own processes or air conditioning systems, or additional modules can be combined to make an DEW Plus. The DEW Plus provides additional process air filtration, cooling, heating and mixing functions that many end users require. The DEW Plus arrangement is skid-mounted, providing a single source, factory assembled package.

These modular dehumidifiers are used in a wide variety of applications from; static and active storage (ie: preposition asset storage (land and sea based)), weapons and ammunition production facilities, all levels of repair facilities (organizational, intermediate and depot level), and operational readiness applications for a broad range of military tactical and communication platforms.



DEW Series Modular Desiccant Dehumidifiers

DEW Series Standard Technical Specifications and Advanced Features

Nominal SCFM	Moisture Removal (lbs/hr) at 75 °F, 50% RH	General Dimensions L x W x max H (in.)	General Weight (lbs.)	Typical ESP (in. W.G.)	
				Process	React
600	16	76 x 31 x 56	400	3.5	2.75
1,125	30	130 x 37 x 72	925	3.5	1.4
2,250	60	146 x 47 x 80	1,150	3.75	1.65
4,500	120	146 x 66 x 98	2,050	2.5	2.3
9,000	240	169 x 85 x 112	3,100	1.9	0.8

* Dimensions and weight are approximate

Utilities: 208, 230, 460 or 575 volts

Reactivation Heaters:

EA-Electric: 208-575 volts

SA-Steam: 10-150 psig

GA/DGA-Gas: Natural or propane

4.5 to 14" W.G. pressure


Reactivation Filter: Permanent and washable

Electric Controller: NEMA 4

Installation: Indoor or outdoor

Options: On/off or modulating humidity control, internal or external bypass, skirts, weatherhoods, pre- and post-air treatment modules can include filtration, cooling and heating

DEW-Plus (DEW Dehumidifier with Add-on Modules)



1 Process Air Blower Plenum

The process air blower plenum is insulated to avoid condensation when process air temperature is below the dewpoint of surrounding air. Also, the process air blower plenum provides in-line airflow to the mixing box, coil module or ductwork.

2 Mixing Plenum

The mixing plenum allows incoming air to be mixed with up to four other incoming air streams. Manual dampers are provided to balance the airflows. The mixed air stream can then be further conditioned by downstream modules.

3 Post-Heat/Cool Coil Plenum

5 Pre-Heat/Cool Coil Plenum

The coil plenum is designed to house a maximum of 10 rows of coils for direct expansion refrigeration, chilled water, hot water, steam or combinations to provide pre- or post-cooling or heating. Alternatively, electric heating elements can also be housed in this plenum. The maximum face velocity is 500 fpm for cooling coils and 900 fpm for heating coils/elements.

4 Face and Bypass Plenum

The face and bypass plenum provides 100% bypass capabilities. Face and bypass dampers of low leakage design are operated by proportioning actuators.

6 Filter Plenum, 30%

7 Filter Plenum, High Efficiency

A disposable filter of 30% efficiency has slide rails that provide easy access for maintenance. A disposable, high efficiency filter of up to 95% (combined with disposable 30% efficiency pre-filter) has slide rails that provide easy side access for maintenance. Consult factory for HEPA filters and plenums.

8 Skid

A structural aluminum skid of "C" channel design is between 6" to 10" in height. On smaller units, with shorter lead times, formed steel can be utilized.

DEW Series Advanced Features

Contact Air Seals:

Separate process and reactivation air at pressures up to 8" W.G. with a five year life expectancy.

Process & Reactivation Fans:

Centrifugal, direct drive with totally enclosed fan cooled motors.

Electrical Controls:

Continuous automatic operation including motor starters, overload protective devices, microprocessor with indicating lights and fault circuits. All wiring to NEC codes.

Drive System:

Simple, self-tensioning drive belt arrangement, few moving parts.

Reactivation Utility:


Electric with solid state proportioning control, steam with proportional air volume control or gas (direct/indirect) with modulating gas valve.

Dehumidifier Housing:

Process and reactivation air flow insulation. Durable air-dry polyurethane paint. All welded aluminum cabinet.

Desiccant Rotor:

In the 1950s, Munters invented modern industrial dehumidification when it introduced the self-regenerating desiccant rotor, the heart of the dehumidifier.



Australia Munters Pty Limited, Phone +61 2 6025 6422, Fax +61 2 6025 8266, **Austria** via sales organization in Germany, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, Fax +55 41 3317 5070, **Canada** Munters Canada Inc., Phone +1 416 271 9657, **China** Munters Air Treatment Equipment (Beijing) Co., Ltd., Phone +86 10 80 483 493, **Denmark** via sales organization in Sweden, **Finland** Munters Oy, Phone +358 9 83 86 030, Fax +358 9 83 86 0336, **France** Munters France S.A., Phone +33 1 34 11 57 50, Fax +33 1 34 11 57 51, **Germany** Munters Euroform GmbH, Phone +49 241 89 00 0, Fax +49 241 89 00 5199, **Indonesia** Munters, Phone +62 21 9105446-7, Fax +62 21 5310509, **Italy** Munters Italy S.p.A., Phone +39 0183-52 11, Fax +39 0183-521 333, **Japan** Munters K.K., Phone +81 3 5970 0021, Fax +81 3 5970 3197, **Kingdom of Saudi Arabia** and **Middle East** **Hawa** Munters, c/o Hawa United Cooling Syst. Co. Ltd., Phone +966 1 477 15 14, Fax +966 1 476 09 36, **Korea** Munters Korea Co., Ltd, Phone +82 2 761 8701, Fax +82 2 761 8777, **Mexico** Munters Mexico Phone +52 722 270 40 30, Fax +52 722 270 41 95, **Norway** via sales organization in Sweden, **South Africa** and **Sub-Saharan Countries** Munters (Pty) Ltd, Phone +27 11 997 2000, Fax +27 11 608 3501, **Spain** Munters Spain S.A., Phone +34 91-640 09 02, Fax +34 91-640 11 32, **Sweden** Munters Europe AB, Phone +46 8 626 63 00, Fax +46 8 754 56 66, **Switzerland** via sales organization in Germany, **Thailand** Munters (Thailand) Co. Ltd., Phone +66 2 645 2708-12, Fax +66 2 645 2710, **United Kingdom** Munters Ltd, Phone +44 845 644 3980, Fax +44 845 644 3981, **United States** Munters Corporation, Phone +1 800 843 5360, **Export & other countries** Munters, Phone +46 8 626 63 00, Fax +46 8 754 56 66.



Your closest distributor

Munters Corporation

Tel: (800) 843-5360 E-mail: dhinfo@munters.com www.munters.us