

DEW-600 Modular Desiccant Dehumidifier with Options

Benefits

- Weather-tight construction for indoor or outdoor use
- Low profile cassette design
- Quick access for easy maintenance
- Easy duct connections
- Modulating electric or steam reactivation
- Multiple blower orientations
- Optional built-in bypass
- Add-on post/pre-air treatment options

DEW-600 Modular Desiccant Dehumidifier with Options

Process Air: Flow rates of 300-1125 scfm. Nominal moisture removal: 16 lbs/hr at 75°F, 50% RH at 600 scfm. Delivered air moisture levels of -40°F dewpoint and lower are attainable.

Contact Air Seals: Separate process and reactivation air at pressures up to 8" W.G. with 5 years life expectancy.

Process & Reactivation Fans: Centrifugal, direct drive with totally enclosed fan cooled motors.

Electrical Controls: Continuous automatic operation including motor starters, overload protective devices, programmable logic controller with indicating lights and fault circuits. All wiring to NEC codes.

Drive System: Simple drive belt arrangement, few moving parts.

Reactivation Utility: Electric with solid state proportioning control or steam with proportional air volume control.

Dehumidifier Housing: Process and reactivation air flow insulation. Durable air-dry polyurethane paint. All welded aluminum cabinet.



DEW-600 Modular Desiccant Dehumidifier


DEW-600 Dimensions Table for EA (Electric) and SA (Steam) Reactivation

Model	Max Length (in.)	Max Width (in.)	Max Height (in.)	Max Weight (lbs.)	Typical External Static Pressures (in. W.G.)	
					Process	React
DEW-600 EA	58	31	56	400	3.5	2.75
DEW-600 SA	76	31	56	410	3.5	2.75

Typical Energy Consumption

Model EA Voltage	Heater kW	Unit Amps
208	13.5	51
230	13.5	45
460	13.5	23
575	13.5	18

Model DEW-600 - EA (Electric)



DEW-600 Suggested Specification Guide

Dehumidifier shall be of a type proven in satisfactory operation for a minimum of ten years. Dehumidifier shall be of the non-cycling sorption type with a single desiccant rotary structure. The casing will be fabricated as a unitized body with welded aluminum construction for maximum strength and durability. Suitable access panels on both sides of the unit shall allow access for inspection or servicing without disconnecting ducting or electrical wiring. Airflow balancing dampers to be furnished. The dehumidifier shall be designed for continuous operation.

The rotary structure shall be a monolithic fabricated extended surface consisting of inert silicates reinforced with uniform diameter glass fibers for maximum strength. The fabricated structure shall be smooth and continuous in the direction of airflow without interruptions or sandwich layers which restrict airflow

or create a leakage path at joining surfaces. Desiccant shall not channel, cake or fracture due to repeated temperature and moisture cycling. The materials of construction shall be non-toxic and NFPA 255-ASTM E84 compliant.

The desiccant wheel shall be a single piece for fast removal and simple handling. The desiccant wheel shall be supported by four rollers at the base of the unit so the wheel can be easily removed for maintenance by lifting it over the rollers using the drive belt. Center-axle support or any arrangement which requires disassembly of the support structure for wheel removal shall not be acceptable.

Design shall be modular in approach to readily allow connection to accessories such as face & bypass, pre- or post-cool modules.

Electrical components shall be UL/CSA recognized

Technical Specifications*

Utilities: 208, 230, 460 or 575 volts

Reactivation Heaters:

EA-Electric: 208-575 volts

SA-Steam: 10-150 psig

Max Reactivation Air Volume: 230 scfm

Reactivation Filter: Permanent and washable

Electric Controller: NEMA 4

Installation: Indoor or outdoor


Options: On/off or modulating humidity control, internal or external bypass, skirts, weatherhoods, pre- and post-air treatment modules can include filtration, cooling and heating

* Continual engineering and research for product improvement may result in design and specification changes. Consult factory for certified technical data.

Desiccant Rotors

In the 1950's, Munters invented modern industrial dehumidification when it introduced the self-regenerating desiccant rotor, the heart of the dehumidifier.

Today, Munters offers rotors with six desiccant formulations and is the acknowledged expert in the integration of rotors into dehumidification systems and air handlers.



and wiring methods in accordance with the latest edition of the National Electric Code. Power supply shall be ___Volts/3 Phase/___ Hertz.

Full face contact pressure seals shall be provided to separate the process and reactivation air streams and eliminate detrimental leakage of air or moisture with static pressure differentials of up to 8" of water gauge.

Dehumidifier shall be factory assembled, fully automatic, complete with HoneyCombe desiccant wheel, reactivation heaters, reactivation energy control system, roughing filters, motors, fans, non-ratcheting desiccant drive unit, automatic controller and all components' auxiliaries. Dehumidifier shall be functionally tested at the manufacturer's factory and shipped complete with all components necessary to maintain normal operation.

Australia Munters Pty Limited, Phone +61 2 6025 6422, Fax +61 2 6025 8266, **Austria** via sales organization in Germany, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, Fax +55 41 3317 5070, **Canada** Munters Canada Inc., Phone +1 416 271 9657, **China** Munters Air Treatment Equipment (Beijing) Co., Ltd., Phone +86 10 80 481 121, Fax +86 10 80 483 493, **Denmark** via sales organization in Sweden, **Finland** Munters Oy, Phone +358 9 83 86 030, Fax +358 9 83 86 0336, **France** Munters France S.A., Phone +33 1 34 11 57 50, Fax +33 1 34 11 57 51, **Germany** Munters Euroform GmbH, Phone +49 241 89 00 0, Fax +49 241 89 00 5199, **Indonesia** Munters, Phone +62 21 9105446-7, Fax +62 21 5310509, **Italy** Munters Italy S.p.A., Phone +39 0183-52 11, Fax +39 0183-521 333, **Japan** Munters K.K., Phone +81 3 5970 0021, Fax +81 3 5970 3197, **Kingdom of Saudi Arabia** and **Middle East** **Hawa** Munters, c/o Hawa United Cooling Syst. Co. Ltd., Phone +966 1 477 15 14, Fax +966 1 476 09 36, **Korea** Munters Korea Co., Ltd, Phone +82 2 761 8701, Fax +82 2 761 8777, **Mexico** Munters Mexico Phone +52 722 270 40 30, Fax +52 722 270 41 95, **Norway** via sales organization in Sweden, **South Africa** and **Sub-Sahara Countries** Munters (Pty) Ltd, Phone +27 11 997 2000, Fax +27 11 608 3501, **Spain** Munters Spain S.A., Phone +34 91-640 09 02, Fax +34 91-640 11 32, **Sweden** Munters Europe AB, Phone +46 8 626 63 00, Fax +46 8 754 56 66, **Switzerland** via sales organization in Germany, **Thailand** Munters (Thailand) Co. Ltd., Phone +66 2 645 2708-12, Fax +66 2 645 2710, **United Kingdom** Munters Ltd, Phone +44 845 644 3980, Fax +44 845 644 3981, **United States** Munters Corporation, Phone +1 800 843 5360, **Export & other countries** Munters, Phone +46 8 626 63 00, Fax +46 8 754 56 66.



Your closest distributor
Munters Corporation
 Tel: (800) 843-5360 E-mail: dhinfo@munters.com www.munters.us