

A MUNTERS ORIGINAL PART

GLASdek®IV

Fire Rated Evaporative Cooling
and Humidification Media

GLASdek®

- High evaporative efficiency
- Fire Rated UL®900,
ULC-S111 Class 1
- GREENGUARD Gold certified
- High face velocity, low pressure drop,
low drift
- Self-cleaning design

Optional TUFedg®:

- Protective edge coating
- Algae and weather resistant
- Extends the service life of
evaporative pads
- Scrubbable

GLASdek®IV

The new generation fire rated evaporative media

Munters is proud to introduce a new and improved generation of its fire rated evaporative cooling media.

Munters GLASdek, the original evaporative media, was invented by Munters in the 1970's. The unique design has continuously been developed for maximum operating efficiency, safety and life span. The shallow angle of Munters unequal flute design allows high velocity air to travel through the pad without significant resistance or water droplet carry over. GLASdeks' self-cleaning design resists clogging caused by dust, sand or other debris. By design, more water is directed toward the air entering face of the pad, where it flushes away dirt and debris while allowing maximum cooling performance (See Figure 1). Our new generation media, GLASdek® IV, has increased strength and durability with exceptional cooling and humidification rates due to its design, manufacturing and materials. It is made from a flame retardant material fortified with special rigidifying agents, and is the evaporative cooling and humidification media choice where strict adherence to fire codes is required. Fire Rated UL®900 and ULC-S111 Class 1.

The new generation pad has tested better or equal in every aspect, with a better resistance to supply water conditions and harsh environments, as well as improved drift properties. When properly maintained, Munters GLASdek pads will provide many years of efficient cooling and humidification. GLASdek® IV is also GREENGUARD Gold certified under UL's certification program, as having low chemical emissions, validating that it meets the highest industry standards globally.




TUFedg® as an option

For extended service life, Munters offers the option of TUFedg. A tough and resilient edge treatment which is applied to the air entering face of a GLASdek pad. It has been formulated to withstand repeated cleaning without damaging the pad.

Munters TUFedg is non-porous and quick drying. It prevents algae and minerals from anchoring themselves into the substrate of the pad, so they slough off when dried. TUFedg also protects GLASdek pads from damaging effects of severe weather and long term exposure to UV light. This protective edge coating extends the life of the pad.

Distribution pad as an option

These pads disperse water laterally and evenly across the top of the pad. These specifically designed pads can also be protected with Munters patented edge treatment.



Design Considerations

Water flow needed is based on the depth and height of the media used. GLASdek typically requires 1.5 gallons per minute per square foot of horizontal (top) pad surface area for 72" tall pads.

Supply: the gutter and sump should be sized to supply the system with enough water to operate at its maximum flow rate and not overflow when the system is shut down.



Munters GLASdek IV

Maintenance

Mineral deposits can be minimized by maintaining a continuous water bleedoff, or by periodically dumping the sump. The exact amount will depend on the pH and hardness of the water supply. Munters can assist by recommending individual bleed-off rates.

Early implementation of simple maintenance techniques prevents algae build up. The efficiency of the pad is maintained when the air can flow uninhibited through the pad. Munters maintenance bulletins provide information to help maximize the efficiency and life of GLASdek.

Pad Sizes Available

Depth: 4", 6", 8", 12", 18"
Height: 48", 60", 72"
Width: 12"

Selection

The depth and height of the media varies by application. Call Munters for help in determining the requirements of specific installations. GLASdek may also be cut to fit smaller equipment.

Australia Phone +61 2 8843 1588, dh.info@munters.com.au **Austria** Phone +43 1 6164298-0, luftentfeuchtung@munters.at **Belgium** Phone +32 1528 5611, info@muntersbelgium.be **Brazil** Phone +55 41 3317 5050, munters@com.br **Canada** Phone +1 905 858 5894, dhinfo@munters.com **China** Phone +86 10 8041 8000, info@munters.com.cn **Czech Republic** Phone +420 544 211 434, info@munters-odvlhcovani.cz **Denmark** Phone +45 4495 3355, info@munters.dk **Finland** Phone +358 20 776 8230, laitemyynit@munters.fi **France** Phone +33 1 3411 5757, dh@munters.fr **Germany** Phone +49 4087 96900, mgd@munters.de **India** Phone +91 20 668 18 900, info@munters.in **Italy** Phone +39 0183 52 11, marketing@munters.it **Japan** Phone +81 3 5970 0021, mkk@munters.co.jp **Korea** Phone +82 2761 8701, munters@munters.co.kr **Mexico** Phone +52 722 270 40 49, munters@munters.com.mx **Netherlands** Phone +31 172 433231, vochibeheersing@munters.nl **Poland** Phone +48 58305 3517, dh@munters.pl **Singapore** Phone +65 6744 6828, info@munters.com.sg **South Africa** Phone +27 11 997 2000, info@munters.co.za **Spain** Phone +34 91 640 09 02, marketing@munters.es **Sweden** Phone +46 8 626 63 00, avfukning@munters.se **Switzerland** Phone +41 52 343 8886, info.dh@munters.ch **Thailand** Phone +66 2642 2670, info@munters.co.th **Turkey** Phone +90 216 548 1444, info@muntersform.com **UAE** +971 4887 6462, middle.east@munters.com **United Kingdom** Phone +44 1480 432243, info@munters.co.uk **USA** Phone +1 978 241 1100, dhinfo@munters.com **Vietnam** Phone +84 8 8256 838, vietnam@muntersasia.com



Your closest distributor

Tel: +1 800 843 5360 E-mail: dhinfo@munters.com www.munters.us