


Zeolite Rotor Cassette Energy Efficient VOC Abatement



Benefits

- 100% inorganic, eliminating fire risk
- No solvent buildup due to 100% rotor regeneration
- Regeneration occurs at 182°C, reducing energy costs
- Size ranges from 2190 to 4800 mm diameter to accommodate various flow rate specifications


Zeolite Rotor Cassette – Energy Efficient VOC Abatement

Munters Zeolite Rotor Cassettes are the leading technology for abatement of volatile organic compounds (VOCs). With more than 300 systems currently in service, our install base includes some of the world's most respected companies. Munters pioneered the development of the hydrophobic zeolite for VOC adsorption over 60 years ago and manufactures the rotor and cassette in our ISO 9001:2015 Certified US facility.

Munters uses a proprietary mixture of zeolites with different pore sizes to cover a wide range of VOC molecule sizes. The pore sizes are all consistent which prevents large molecules from blocking active adsorption sites. These parameters make Munters zeolite rotors 100% inorganic and, therefore, have zero risk of fire unlike carbon adsorbers.

The sectors of the Munters zeolite rotor are bolted together versus glued, allowing for easy replacement if necessary. Rotor rotation is powered by a fractional horsepower motor and redundant belt around the circumference of the rotor. The drive motor and redundant belt provide a robust assembly and increased reliability. (Please refer to Rotor Drive Assembly image on reverse side).

As a result of aluminum construction, Munters zeolite rotors are corrosion resistant and lightweight. Rotors are available in multiple sizes to handle a wide range of flow rates and can ship via standard shipping containers (rotors 2446 mm in diameter and larger will require breakdown for shipment).



Maintenance-free, Self-cleaning Design

Munters engineers optimize each system for maintenance-free design including a self-cleaning feature that ensures 100% zeolite regeneration and zero buildup of VOCs on the rotor during every revolution. High performance efficiency is maintained for the life of the rotor without the need for nuisance maintenance activities like water washing and high temperature bake-outs.



Scope of Supply

- Hydrophobic zeolite rotor
- Painted aluminum casing
- Gear reducer
- Rotor drive assembly
IEC: 400V / 50Hz
or
Dual Rated NEMA:
230/460 V / 60Hz
190/380 V / 50Hz
- Rotor hub and spokes
- Elastometer seals

Rotor Sizing

Rotor Diameter	Depth	Flow Range (NCMH)	Dimensions (L x W x H)
2190 mm	400 mm	9,000 - 44,000	2.4 x 0.9 x 2.4
2446 mm	400 mm	12,000 - 60,000	2.8 x 0.9 x 2.7
2946 mm	400 mm	18,000 - 88,000	3.2 x 0.9 x 3.1
3546 mm	400 mm	25,000 - 128,000	3.8 x 0.9 x 3.7
4200 mm	400 mm	36,000 - 182,000	4.5 x 0.9 x 4.3
4800 mm	400 mm	47,000 - 236,000	5.1 x 1.2 x 5.0


Zeolite Rotor Technology



Industries Served

- Semiconductor
- TFT/LCD (flat panel display manufacturing)
- Automotive paint finishing
- Aerospace paint finishing
- Coating
- Printing/Packaging
- Composite manufacturing

Rotor Drive Assembly



Australia Phone +61 2 8843 1580, serviceair@munters.com.au Austria Phone +43 1 6164298-0, service.dh@munters.at Belgium & Luxembourg Phone +32 (0) 15 28 56 11, info@muntersbelgium.be Brazil Phone +55 41 3317 5050, munters@com.br Canada Phone +1 905 858 5894, dhinfo@munters.com China Phone +86 10 8041 8000, serviceair@munters.cn Czech Republic Phone +420 544 211 434, servicecz@munters.de Denmark Phone +45 4495 3355, service.dh@munters.dk Finland Phone +358 40 186 3074, service.dh@munters.fi France Phone +33 1 3411 5757, service.dh@munters.fr Germany Phone +49 40 87 96 90-0, service.dh@munters.de India Phone +91 20 6681 8900, serviceair@munters.in Italy Phone +39 0183 521 377, service.dh@munters.it Japan Phone +91 3 5970 0021, serviceair@munters.jp Korea +82 2 761 8701, serviceair@munters.co.kr Mexico Phone +52 722 270 4029, servicedhm@munters.com Netherlands Phone +31 172 43 32 31, service@munters.nl Poland Phone +48 58 305 35 17, service.dh@munters.pl Singapore Phone +65 6744 6828, serviceair@munters.com.sg South Africa Phone +27 11 971 9700, info@munters.co.za Spain & Portugal Phone +34 91 640 09 02, service.dh@munters.es Sweden & Norway Phone +46 8 626 6300, service.dh@munters.se Switzerland Phone +41 52 3438886, service.dh@munters.ch Thailand Phone +66 2 6422 6703, serviceair@munters.com.sg Turkey Phone +90 216 548 1444, serviceair@munters.com.tr UAE +971 4881 3026, middle.east@munters.com United Kingdom & Ireland Phone +44 1480 432243, service.dh@munters.co.uk USA Phone +1 800 843 5360, dhinfo@munters.com Vietnam Phone +84 8 3825 6838, vietnam@muntersasia.com



Munters Corporation

Tel: (800) 843-5360 E-mail: dhinfo@munters.com
www.munters.com